



Tool Make & Model

Producer GT

Tool Configuration / Specifications

Does not include: Dry pumps, Chillers, HDD, RPS X 3pcs , AC Rack , Monitors, ADVANCED ENERGY APRX3013 RF Generator.

Process Type: CVD deposition

Software Version: -

Number of Chambers: 3

Load Locks LL1, LL2: LL1, LL2

Transfer Chamber: Vacuum Robot

Process Chambers: PECVD Deposition

ESC Type : Heater

Factory Interface: EFEM + FOUP Load Ports

Communications: SECS/GEM, GEM300

Utilities: CDA, N₂, Process Gas, Cooling Water, Vacuum

Safety Systems: Gas Monitoring, Interlocks, EMO

Monitors: Nil

Browse our site at www.moov.co

The information contained in this data sheet is, to our knowledge, accurate. We do not warrant the completeness or accuracy of the information contained herein. Any offer by you to purchase the equipment described in this data sheet shall be subject to the terms and conditions of sale.