

## Transaction Information

|                     |           |
|---------------------|-----------|
| Tool ID             |           |
| Tool Status         | Connected |
| Location            |           |
| Wafer Size          | 200 mm    |
| Fab Section         | Thin Film |
| Tool Available Date |           |

## General Product Information

|                   |              |
|-------------------|--------------|
| Vendor Supplier   | AMAT         |
| Model             | CENTURA 5200 |
| Vintage           | 1997         |
| Serial No         |              |
| Asset Description | TF0045       |
| Software Version  | E3.240       |
| CIM               | SECS         |
| Process           | PASSIVATION  |

## Hardware Configuration

| System Type       | Description       | Quantity |
|-------------------|-------------------|----------|
| Handler System    | LL & Buffer       | 1        |
| Options System    | process chamber   | 4        |
| Main System       | Mainframe         | 1        |
| Factory Interface | NONE              |          |
| Others            | SYSTEM CONTROLLER | 1        |

| Description | Quantity |
|-------------|----------|
| MFA         | 2        |
| DRY PUMP    | 6        |

| Description | Quantity |
|-------------|----------|
| 2K2VGEN     | 2        |
| HDD         | 2        |
| DPA Gen     | 3        |
| SBC BD      | 1        |